

# ANTISTATIC DISPOSABLE COVERALL

603-3008 - 603-3015

Integrity® Cleanroom Apparel products are designed and manufactured to meet the stringent demands of the cleanroom industry. Manufactured from microporous material, our products provide excellent comfort, breathability and water vapour transmission rates. Our product meets PPE Standard Category 3, Type 5 & 6 offering a cost effective option for your disposable apparel requirements. Our products are available sterile by Gamma Irradiation and are ISO4, EU GMP Grade A Compatible.

## FEATURES

- Anti-static
- 55 gsm
- Zip Closure
- Elastic Cuffs
- Includes Hood

| PRODUCT CODE | SIZE     | ANTISTATIC |
|--------------|----------|------------|
| 603-3008     | Small    | Yes        |
| 603-3009     | Medium   | Yes        |
| 603-3010     | Large    | Yes        |
| 603-3011     | X-Large  | Yes        |
| 603-3012     | 2X-Large | Yes        |
| 603-3013     | 3X-Large | Yes        |
| 603-3014     | 4X-Large | Yes        |
| 603-3015     | 5X-Large | Yes        |

## PACKAGING

1 pc/bag, 50 bags/case, 50 pcs/case.



To request a quotation or for more information, please call **+1 512-713-0127**, email [info@integritycleanroom.com](mailto:info@integritycleanroom.com) or visit [www.integritycleanroom.com](http://www.integritycleanroom.com).

IMPORTANT: This data sheet and its contents (the "Information") belong to Integrity Cleanroom or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but Integrity Cleanroom assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where Integrity Cleanroom was aware of the possibility of such loss or damage arising) is excluded. © Integrity Cleanroom.



**Integrity US**  
Round Rock, Texas




**Integrity UK**  
Bury St Edmunds, Suffolk



**Integrity DE**  
Nuremberg, Bavaria





| DESCRIPTION                         | # ON GRAPHIC | MEDIUM (in) | LARGE (in) | X-LARGE (in) | 2X-LARGE (in) | TOLERANCE 1+/-1 (in) |
|-------------------------------------|--------------|-------------|------------|--------------|---------------|----------------------|
| Overall Length                      | 1            | 61          | 66.9       | 72.04        | 72.8          | +/- 1 in             |
| Torso Length                        | 2            | 34.6        | 36.2       | 40.5         | 41.3          | +/- 1 in             |
| Zipper Length                       | 3            | 25.5        | 25.5       | 29.9         | 30.7          | +/- 1 in             |
| Inseam                              | 4            | 27.9        | 30.7       | 32.2         | 33.07         | +/- 1 in             |
| Chest Width                         | 5            | 25.9        | 26.7       | 29.5         | 29.5          | +/- 1 in             |
| Waist Size (before elastic sewn in) | 6            | 25.9        | 26.7       | 29.5         | 29.5          | +/- 1 in             |
| Overall Arm Length                  | 7            | 65.7        | 68.8       | 73.6         | 74            | +/- 1 in             |
| Sleeve Length (from underarm seam)  | 8            | 19.6        | 21.2       | 22.04        | 22.2          | +/- 1 in             |
| Sleeve Width                        | 9            | 10.03       | 10.2       | 10.4         | 10.6          | +/- 1 in             |
| Relaxed Wrist (elastic) Opening     | 10           | 2.7         | 3.1        | 3.1          | 3.3           | +/- 1 in             |
| Stretched Wrist (elastic) Opening   | 11           | 6.2         | 6.4        | 6.4          | 6.6           | +/- 1 in             |
| Relaxed Ankle (elastic) Opening     | 12           | 4.7         | 5.9        | 5.9          | 6.2           | +/- 1 in             |
| Stretched Ankle (elastic) Opening   | 13           | 7.4         | 8.2        | 8.2          | 8.8           | +/- 1 in             |
| Hood Height/Stretched Hood Opening  | 14           | 12          | 12.2       | 12.2         | 12.5          | +/- 1 in             |
| Hood Width                          | 15           | 4.7         | 5.1        | 5.1          | 5.5           | +/- 1 in             |
| Relaxed Hood Opening                | 16           | 6.2         | 6.6        | 6.6          | 7.08          | +/- 1 in             |



To request a quotation or for more information, please call **+1 512-713-0127**, email [info@integritycleanroom.com](mailto:info@integritycleanroom.com) or visit [www.integritycleanroom.com](http://www.integritycleanroom.com).

IMPORTANT: This data sheet and its contents (the "Information") belong to Integrity Cleanroom or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but Integrity Cleanroom assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where Integrity Cleanroom was aware of the possibility of such loss or damage arising) is excluded. © Integrity Cleanroom.



**Integrity US**  
Round Rock, Texas



**Integrity UK**  
Bury St Edmunds, Suffolk



**Integrity DE**  
Nuremberg, Bavaria



# ANTISTATIC DISPOSABLE COVERALL

603-3008 - 603-3015

| DESCRIPTION                  | INTEGRITY RESULT | TEST PROCEDURE PGI STANDARD | REF TEST PROCEDURE ASTM STANDARD |
|------------------------------|------------------|-----------------------------|----------------------------------|
| Basis Weight oz/yd           | 1.5 (55 gsm)     | D3776                       | D3776                            |
| Thickness Mils               | 6.77             | D1777                       | D1777                            |
| Strip Tensile (MD/CD) lbs/in | 8.73/6.22        | D1682                       | D1682                            |
| Strip Elongation (MD/CD) %   | 112/107          | D1682                       | D5034                            |
| Work to Break in - lbs       | 20.38/12.13      | D1682                       | D1682                            |

| ITEM                | INTEGRITY RESULT   | TEST PROCEDURE PGI STANDARD | REF TEST PROCEDURE ASTM STANDARD                             |
|---------------------|--|-----------------------------|--|
| Water Resitance Kpa | ± 8.0 %  | FZ/T 01004-1991             | 18.8   |
| Tear Strength N/5cm | ± 2.6 % for PP/PES/Nomex<br>± 4.1 % for 100% Wool<br>± 5.2 % for 100% Cotton | ASTM D2261-1996             | Sample cut by horizontal side, normal testing cannot be done |
|                     |  |                             | Woof: 8.6  |
| Chemical Resistance | Bleach 5%  | ASTM T903                   | Pass   |
|                     | Hydraulic Jack Oil   | ASTM T903                   | Pass   |
|                     | Isocyanate Based Paint Hardener  | ASTM T903                   | Pass   |
|                     | Motor Oil  | ASTM T903                   | Pass   |
|                     | Sodium Hydroxide   | ASTM T903                   | Pass   |
|                     | Mineral Oil  | ASTM T903                   | Pass   |



To request a quotation or for more information, please call  
**+1 512-713-0127**, email [info@integritycleanroom.com](mailto:info@integritycleanroom.com)  
 or visit [www.integritycleanroom.com](http://www.integritycleanroom.com).

IMPORTANT: This data sheet and its contents (the "Information") belong to Integrity Cleanroom or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but Integrity Cleanroom assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where Integrity Cleanroom was aware of the possibility of such loss or damage arising) is excluded. © Integrity Cleanroom.



**Integrity US**  
Round Rock, Texas



**Integrity UK**  
Bury St Edmunds, Suffolk



**Integrity DE**  
Nuremberg, Bavaria

